






DE - MONTAGEANWEISUNG
 FR - INSTRUCTIONS DE MONTAGE
 DK - MONTAGEVEJLEDNING
 CZ - NÁVOD K MONTÁŽI
 ES - INSTRUCCIONES DE MONTAJE
 FI - ASENNUSOHJE

HR - UPUTE ZA MONTAŽU
 BE - MONTERINGSANVISNING
 SI - NAVODILA ZA MONTAŽO
 TR - MONTAJ TALIMATI
 NO - MONTASJEANVISNING
 IT - ISTRUZIONI DI MONTAGGIO

GR - ΟΔΗΓΙΑ ΣΥΝΑΡΜΟΛΟΓΗΣΗΣ
 NL - MONTAGE INSTRUCTIE
 PT - INSTRUÇÕES DE MONTAGEM
 PL - INSTRUKCJA MONTAŻU
 HU - SZERELÉSI UTASÍTÁS





ASSEMBLY INSTRUCTION


DE - MONTAGEANWEISUNG
 FR - INSTRUCTIONS DE MONTAGE
 DK - MONTAGEVEJLEDNING
 CZ - NÁVOD K MONTÁŽI
 ES - INSTRUCCIONES DE MONTAJE
 FI - ASENNUSOHJE

HR - UPUTE ZA MONTAZU
 NO - MONTERINGSANVISNING
 NI - NAVODILA ZA MONTAŽO
 TR - MONTAJ TALIMATI
 NO - MONTASJANVISNING
 IT - ISTRUZIONI DI MONTAGGIO








GR - ΟΔΗΓΙΑ ΣΥΝΑΡΜΟΛΟΓΗΣΗΣ
 NL - MONTAGE INSTRUCTIES
 PT - INSTRUÇÕES DE MONTAGEM
 PL - INSTRUKCJA MONTAŻU
 HU - SZERELÉSI UTASÍTÁS





20 min



- ① HW-ST-01-041 (7 x 55) x 6
- ② HW-ST-01-046 (7 x 90) x 8
- ③ HW-ST-02-054 (8 x 40) x 4
- ④ HW-PL-03-048 (Ø20 x 14) x 8
- ⑤ HW-ST-01-011 (4 x 35) x 12
- ⑥ HW-ST-03-014 (8 x 13) x 4
- ⑦ HW-ST-18-001 (4 x 98) x 2





ASSEMBLY INSTRUCTION



DE - MONTAGEANWEISUNG
 FR - INSTRUCTIONS DE MONTAGE
 DK - MONTAGEVEJLEDNING
 CZ - NÁVOD K MONTÁŽI
 ES - INSTRUCCIONES DE MONTAJE
 FI - ASENNUSOHJE

HR - UPUTE ZA MONTAŽU
 NF - MONTFRINGSANVISNING
 NI - NAVODILA ZA MONTAŽO
 TR - MONTAJ TALIMATI
 NO - MONTASJEANVISNING
 IT - ISTRUZIONI DI MONTAGGIO


GR - ΟΔΗΓΙΑ ΣΥΝΑΡΜΟΛΟΓΗΣΗΣ
 NL - MONTAGE INSTRUCTIES
 PT - INSTRUÇÕES DE MONTAGEM
 PL - INSTRUKCJA MONTAŻU
 HU - SZERELÉSI UTASÍTÁS







25 min






- ① x 6 HW-ST-01-041 (7 x 55)
- ② x 8 HW-ST-01-046 (7 x 90)
- ③ x 4 HW-ST-02-054 (8 x 40)
- ④ x 8 HW-PL-03-048 (Ø20 x 14)
- ⑤ x 12 HW-ST-01-011 (4 x 35)
- ⑥ x 4 HW-ST-03-014 (8 x 13)
- ⑦ x 2 HW-ST-18-001 (4 x 98)



Ⓔ x 4



Ⓕ x 2



deepseating armchair