

SPEAKMAN COMPANY

S-2590 Installation, Maintenance & Operation Instructions

PIVOTING SHOWER ARM

DESCRIPTION

Speakman polished chrome plated 10" pivoting extension shower arm. Raises or lowers the shower arm over a 20" range. Key included to set adjustment.

SPECIFICATIONS

½" NPSM FEMALE INLET
½" NPT MALE OUTLET
SHIPPING WEIGHT: XXX LBS.

OPTIONS

| | |
|--|---|
| ◇ PBL – Polished Brass Lacquer Finish | ◇ |
| ◇ | |


INSTALLATION

Apply teflon tape or pipe dope to outlet threads of extension arm. Attach shower head. Wrench tighten. Attach extension arm to shower arm using the rubber washer. Wrench tighten. Loosen adjusting nuts and set to desired height, tighten nuts firmly. Check all connections for leaks.

MAINTENANCE

The gleaming finish of your SPEAKMAN pivoting shower arm can be cleaned by using mild soap and warm water. Dry immediately with a soft, clean cloth for best results.

ROUGH-IN MEASUREMENTS



Product improvements may cause
specification and dimensional
changes without notice.